

Fiber Optic Panel, 1U, unloaded, for holding up to 3 LGX/1000 modules, black

## Product Classification

Regional Availability	Asia   China
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	1000-style
General Specifications	
Application	Accepts three LGX/1000 footprint panels/cassettes
Cable Exit Location	Rear, left side   Rear, right side
Color	Black
Growth Configuration	Unloaded
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	3
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding
Splice Trays Included, quantity	0
Total Ports, quantity	0
Dimensions	
Height	43.7 mm   1.72 in
Width	482.6 mm   19 in
Depth	308.1 mm   12.13 in

## Material Specifications

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024



## 760241725

Finish		Powder coated	
Material Type		Steel	
Packaging and Weights			
Included		Mounting hardware	
Packaging quantity		1	
Regulatory Compliance/Certifications			
Agency	Classification		
CHINA-ROHS	Below maximum concentration value		
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system		
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance		
ROHS	Compliant		
UK-ROHS	Compliant		

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

