232268-000 | TDUX-100-INT



Product Classification

TDUX - Inflatable Duct Seal, Size 100

- Flexible and reliable wraparound inflatable sealing system for cables
- Fast and easy to install or remove, even when water is flowing out of the duct
- Independent of duct or cable ovality
- Water and airtight up to 50 kPa (7 psi)
- Environmentaly friendly, non-toxic and resistant to chemicals

PIUUULI LIASSIIILAIIUII	
Regional Availability	EMEA
Product Type	Cable duct seal
Product Series	TDUX
Ordering Note	When sealing more than two cables in a duct, seperate orderable TDUX-CL clips are to be used
Dimensions	
Width	120 mm 4.724 in
Length	482 mm 18.976 in
Cable Diameter, maximum	90 mm 3.543 in
Cable Diameter, minimum	45 mm 1.772 in
Conduit Inner Diameter, maximum	110 mm 4.331 in
Conduit Inner Diameter, minimum	75 mm 2.953 in


Dimension Drawing

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 5, 2024



232268-000 | TDUX-100-INT



Environmental Specifications

Installation temperature

-5 °C to +40 °C (+23 °F to +104 °F)

Packaging and Weights

IncludedInflatable bladder with sealing mechanismPackaging quantity10

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 5, 2024

