CB-12-27LH



Cable banding, 1/2 in x 27 in length with attached locking head, package contains 25 pieces

Product Classification

Product Type

Ordering Note

Banding CommScope® standard product (Global)

General Specifications

Adapter Type	Adapter
Color	Black
Mounting	Round member

Dimensions

Width	12.7 mm 0.5 in
Length	0.686 m 2.25 ft
Material Thickness	1.524 mm 0.06 in

Material Specifications

Material T	уре
------------	-----

Heat-stabilized weather resistant acetal

Mechanical Specifications

Tensile Force	1,112.055 N	250 lbf

Environmental Specifications

Installation temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity 25

Page 1 of 1

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 13, 2024

