

ReadyPATCH® Uniprise® Ready™ Prepopulated Wall Mount Enclosure, black

OBSOLETE

This product was discontinued on: November 5, 2018

Product Classification

Portfolio	Uniprise®
Brand	ReadyPATCH® Ready™
Product Type	Fiber wall box
Regional Availability	North America

Dimensions

Depth	107.95 mm 4.25 in
Height	279.40 mm 11.00 in
Width	330.20 mm 13.00 in

General Specifications

Rack Units	4.0
Adapter Packs Included, quantity	4
Blank Panels Included, quantity	0
Cable Brackets Included, quantity	0
Color	Black
Ordering Note	Adapter panels are installed into the bulkhead from left to right Fiber spools are installed and fiber is dressed on these spools awaiting termination Pigtailed are attached to the adapter panels behind the wall (BTW)
Pigtails Included, quantity	2
Rack Type	EIA 19 in
Splice Trays Included, quantity	1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

760147504 | WBE-EMT-BK-4P-PNL — Ready™ Wall Mount Building Enclosure, 4P, black

760147652 | PNL-BK-006-AFA-SC06-GR — Adapter Pack, Black, 1000-Type, with 1 TeraSPEED® 6 fiber, SM SC/APC ganged adapter, green, shuttered

760057075 | SW-03-FUS — Fusion Splice Wallet Kit with 3 splice trays

FAWSAUC0A — TeraSPEED® SC APC to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer, 6-fiber Kit, Blue - White (1-6)

- X-TB-8W (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125859 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC APC Connector for 0.9 mm Fiber, single-mode

FAWSAUC0B — TeraSPEED® SC APC to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer, 6-fiber Kit, Red - Aqua (7-12)

- X-TB-8W (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125859 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC APC Connector for 0.9 mm Fiber, single-mode



Ready™ Wall Mount Building Enclosure, 4P, black

Product Classification

Portfolio	Uniprise®
Brand	Ready™
Product Type	Fiber wall box
Regional Availability	North America

Construction Materials

Material Type	Steel
----------------------	-------

Dimensions

Depth	107.95 mm 4.25 in
Height	279.40 mm 11.00 in
Width	330.20 mm 13.00 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Application	Accepts four RFE-type adapter panels or ReadyPATCH® modules Accepts Splice Wallet with splice trays
Color	Black

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system





Adapter Pack, Black, 1000-Type, with 1 TeraSPEED® 6 fiber, SM SC/APC ganged adapter, green, shuttered

Product Classification

Portfolio	CommScope®
Brand	TeraSPEED®
Product Series	1000-style
Product Type	Fiber adapter pack
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Mode	Singlemode
-------------------	------------

General Specifications

Interface	SC
Body Style	Ganged
Interface Feature	APC
Adapter Color	Green
Shuttered	No
Adapter Cutout, quantity	1
Adapters, quantity	1
Application	Used in conjunction with panels and enclosures (rack, wall, and floor mount) that accept 1000 style panels Used in conjunction with SD Panels
Total Ports, quantity	6

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system





Fusion Splice Wallet Kit with 3 splice trays

Product Classification

Portfolio	SYSTIMAX®
Product Type	Fiber splice tray
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Application	For G2 4U shelves
Splice Tray Capacity, quantity	3
Splice Trays	Included
Splicing Capacity, maximum	48

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



FAWSAUCOA

TeraSPEED® SC APC to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer, 6-fiber Kit, Blue - White (1-6)

Product Classification

Portfolio	CommScope®
Brand	TeraSPEED®
Product Type	Fiber pigtail, multi-fiber
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	6

Dimensions

Cord Length, maximum	23 ft 7 m
Cord Length, minimum	2 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Plenum
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Construction Type	Pigtail kit
Interface, connector A	SC/APC
Interface, connector B	Unterminated
Color, connector A	Green

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °
--	--------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

X-TB-8W (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber

- CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber

460125859 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC APC Connector for 0.9 mm Fiber, single-mode

FAWSAUCOB

TeraSPEED® SC APC to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer, 6-fiber Kit, Red - Aqua (7-12)

Product Classification

Portfolio	CommScope®
Brand	TeraSPEED®
Product Type	Fiber pigtail, multi-fiber
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	6

Dimensions

Cord Length, maximum	23 ft 7 m
Cord Length, minimum	2 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Plenum
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Construction Type	Pigtail kit
Interface, connector A	SC/APC
Interface, connector B	Unterminated
Color, connector A	Green

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °
--	--------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

X-TB-8W (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber

- CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber

460125859 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC APC Connector for 0.9 mm Fiber, single-mode