

ReadyPATCH® Uniprise® Ready™ Prepopulated Wall Mount Enclosure, black

OBSOLETE

This product was discontinued on: November 5, 2018

Product Classification

Portfolio	Uniprise®
Brand	ReadyPATCH® Ready™
Product Type	Fiber wall box
Regional Availability	North America

Dimensions

Depth	107.95 mm 4.25 in
Height	279.40 mm 11.00 in
Width	330.20 mm 13.00 in

General Specifications

Rack Units	4.0
Adapter Packs Included, quantity	4
Blank Panels Included, quantity	0
Cable Brackets Included, quantity	0
Color	Black
Ordering Note	Adapter panels are installed into the bulkhead from left to right Fiber spools are installed and fiber is dressed on these spools awaiting termination Pigtailed are attached to the adapter panels behind the wall (BTW)
Pigtails Included, quantity	2
Rack Type	EIA 19 in
Splice Trays Included, quantity	1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

760147504 | WBE-EMT-BK-4P-PNL — Ready™ Wall Mount Building Enclosure, 4P, black

760147652 | PNL-BK-006-AFA-SC06-GR — Adapter Pack, Black, 1000-Type, with 1 TeraSPEED® 6 fiber, SM SC/APC ganged adapter, green, shuttered

760057075 | SW-03-FUS — Fusion Splice Wallet Kit with 3 splice trays

FAWSAUC0A — TeraSPEED® SC APC to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer, 6-fiber Kit, Blue - White (1-6)

- X-TB-8W (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125859 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC APC Connector for 0.9 mm Fiber, single-mode

FAWSAUC0B — TeraSPEED® SC APC to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer, 6-fiber Kit, Red - Aqua (7-12)

- X-TB-8W (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125859 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC APC Connector for 0.9 mm Fiber, single-mode