

FD3-MK144J00V00EOB

IFDH 3000 Indoor Fiber Distribution Hub, 144F, loose tube pigtails

Product Classification

Product Type	Fiber distribution hub
Product Series	IFDH 3000
Regional Availability	North America

General Specifications

Adapters, quantity	144
Cable Type	Pigtails - Stranded
Color	Putty white
Distribution Cables, quantity	12
Fibers per Distribution Cable, quantity	12
Fibers per Feeder Cable, quantity	24
Interface Feature, input	APC
Interface, input	SC
Package, quantity	1
Port, quantity	144
Splitter Slots, quantity	18

Dimensions

Depth	368.30 mm 14.50 in
Height	736.60 mm 29.00 in
Width	533.40 mm 21.00 in

Mechanical Specifications

Access	Front
Finish	Powder coated
Front Door Type	Single hinged
Material Type	Steel
Mount Type	Wall

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

