



FibrBoss Wall Mounting Fiber Optic Box, outdoor, 6 LC/APC adapters, with pre-installed pigtails

- Intended as a small patch and splice or fiber “hands-off” enclosure
- Environmentally secure housing for indoor or outdoor wall mounted application
- Accommodates field supplied flat or round drop cable inputs
- Cable retention brackets are integrated into the fiber management tray
- Splice protection sleeves are included to add customer convenience and efficiency

Product Classification

Product Type	Fiber wall box
Product Series	PB06
Regional Availability	Asia Australia/New Zealand Latin America North America

General Specifications

Application	For cables with outer diameter up to 10 mm: each on both sides
Cable Type	Pigtails - Stranded
Enclosure Color	Beige
Functionality	Patching Splicing
Includes	Splice protectors Splice tray
Interface Feature, input	APC
Interface, input	LC
Package, quantity	1
Packaging Type	Box Carton
Port, quantity	6
Splicing Capacity, maximum	6

Dimensions

Depth	60.96 mm 2.40 in
Height	121.92 mm 4.80 in
Width	162.56 mm 6.40 in

Mechanical Specifications

Access	Front
Enclosure Material Type	LSZH thermoplastic
Front Cover Type	Hinged with lock
Lock Type	Padlock ready
Mount Type	Pedestal Pole Wall

Optical Specifications

Fiber Mode	Singlemode
Insertion Loss, Terminal Connector, maximum	0.20 dB
Return Loss, Connector, minimum	55 dB

Environmental Specifications

Environmental Space	Outdoor
Flammability Rating	UL 94 V-0
Qualification Standard	IEC 60529, IP65

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification

