



Rapid Fiber™ EFDT NID Wall Mounting Fiber Box, outdoor, 12 SC/APC, 4-way splitter

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections
- Weatherproof housing suitable for external environmental conditions

Product Classification

Brand	Rapid Fiber™
Product Type	Fiber wall box
Product Series	EFDT
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Distribution Type	1 x 4 splitter
Enclosure Color	Gray
Functionality	Patching Splitting
Interface Feature, input	APC
Interface, input	SC
Package, quantity	8
Packaging Type	Box Carton
Port, quantity	12
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Depth	71.12 mm 2.80 in
Height	264.16 mm 10.40 in
Width	179.07 mm 7.05 in

Mechanical Specifications

Access	Front
Enclosure Material Type	LSZH thermoplastic
Front Cover Type	Hinged with lock
Mount Type	Wall

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A1
Insertion Loss, Splitter, maximum	7.7 dB
Return Loss, Connector, minimum	55 dB
Wavelength Range	1260–1650 nm

Environmental Specifications

Environmental Space	Outdoor
Qualification Standard	IEC 60529, IP55 IEC 61753-1, category G

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

