



Rapid Fiber™ EFDT Wall Mounting Fiber Box, outdoor, 12 SC/APC, HMFOC at far end, 60 m

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections
- Weatherproof housing suitable for external environmental conditions

## Product Classification

<b>Brand</b>	Rapid Fiber™
<b>Product Type</b>	Fiber wall box
<b>Product Series</b>	EFDT
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## General Specifications

<b>Cable Color</b>	White
<b>Cable Type</b>	Microcable - Loose Tube
<b>Enclosure Color</b>	Gray
<b>Functionality</b>	Patching
<b>Interface Feature, input</b>	APC
<b>Interface Feature, stub</b>	APC
<b>Interface, input</b>	SC
<b>Interface, stub</b>	HMFOC
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Port, quantity</b>	12

## Dimensions

<b>Cable Length</b>	60.00 m   196.85 ft
<b>Depth</b>	71.12 mm   2.80 in
<b>Height</b>	264.16 mm   10.40 in
<b>Width</b>	179.07 mm   7.05 in

## Mechanical Specifications

<b>Access</b>	Front
<b>Enclosure Material Type</b>	LSZH thermoplastic
<b>Front Cover Type</b>	Hinged with lock

**Mount Type** Wall

## Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2

**Insertion Loss, Terminal Connector, typical** 0.40 dB

**Return Loss, Connector, minimum** 55 dB

## Environmental Specifications

**Environmental Space** Outdoor

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

