



Rapid Fiber™ EFDT Wall Mounting Fiber Box, outdoor, 12 SC/APC, MPO at far end, 20 m

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections
- Weatherproof housing suitable for external environmental conditions

Product Classification

| | |
|------------------------------|---|
| Brand | Rapid Fiber™ |
| Product Type | Fiber wall box |
| Product Series | EFDT |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

General Specifications

| | |
|---------------------------------|-------------------------|
| Cable Color | White |
| Cable Type | Microcable - Loose Tube |
| Enclosure Color | Gray |
| Functionality | Patching |
| Interface Feature, input | APC |
| Interface, input | SC |
| Interface, stub | MPO |
| Package, quantity | 1 |
| Packaging Type | Box Carton |
| Port, quantity | 12 |

Dimensions

| | |
|---------------------|----------------------|
| Cable Length | 20.00 m 65.62 ft |
| Depth | 71.12 mm 2.80 in |
| Height | 264.16 mm 10.40 in |
| Width | 179.07 mm 7.05 in |

Mechanical Specifications

| | |
|--------------------------------|--------------------|
| Access | Front |
| Enclosure Material Type | LSZH thermoplastic |
| Front Cover Type | Hinged with lock |
| Mount Type | Wall |

Optical Specifications

| | |
|--|------------|
| Fiber Mode | Singlemode |
| Fiber Type | G.657.A2 |
| Insertion Loss, Terminal Connector, typical | 0.40 dB |
| Return Loss, Connector, minimum | 55 dB |

Environmental Specifications

| | |
|----------------------------|---------|
| Environmental Space | Outdoor |
|----------------------------|---------|

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

