



Rapid Fiber™ EFDT Wall Mounting Fiber Box, outdoor, 12 SC/APC, MPO at far end, 80 m

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections
- Weatherproof housing suitable for external environmental conditions

Product Classification

Brand	Rapid Fiber™
Product Type	Fiber wall box
Product Series	EFDT
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Cable Color	White
Cable Type	Microcable - Loose Tube
Enclosure Color	Gray
Functionality	Patching
Interface Feature, input	APC
Interface, input	SC
Interface, stub	MPO
Package, quantity	1
Packaging Type	Box Carton
Port, quantity	12

Dimensions

Cable Length	80.00 m 262.47 ft
Depth	71.12 mm 2.80 in
Height	264.16 mm 10.40 in
Width	179.07 mm 7.05 in

Mechanical Specifications

Access	Front
Enclosure Material Type	LSZH thermoplastic
Front Cover Type	Hinged with lock
Mount Type	Wall

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, Terminal Connector, typical	0.40 dB
Return Loss, Connector, minimum	55 dB

Environmental Specifications

Environmental Space	Outdoor
----------------------------	---------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

