



IWB Fiber Wall Box, 2-door, singlemode FC/UPC, 48-ports, no pigtails, splice tray, 2 cable clamps

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

**OBSOLETE**

This product was discontinued on: March 1, 2018

### Product Classification

<b>Product Series</b>	IWB
<b>Product Type</b>	Fiber wall box
<b>Regional Availability</b>	Asia   EMEA

### Construction Materials

<b>Fiber Mode</b>	Singlemode
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

### Dimensions

<b>Depth</b>	140.00 mm   5.51 in
<b>Height</b>	350.00 mm   13.78 in
<b>Width</b>	505.00 mm   19.88 in

### Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Qualification Standards</b>	NEMA type 12

### General Specifications

<b>Adapters, quantity</b>	48
<b>Application</b>	Patching   Splicing
<b>Color</b>	Gray
<b>Door, quantity</b>	2
<b>Interface Feature, front</b>	Standard
<b>Interface, front</b>	FC
<b>Package Quantity</b>	1

**Packaging Type** Bag | Carton  
**Splice Trays Included, quantity** 0  
**Splicing Capacity, maximum** 48  
**Splicing Type** Mass fusion  
**Total Ports, quantity** 48

## Mechanical Specifications

**Cable Clamps, quantity** 2  
**Cable Entry Location** Bottom right | Top right  
**Front Door Type** Single hinged  
**Mount Type** Wall

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

