



IWB Fiber Wall Box, 2-door, singlemode FC/UPC, 48-ports, with pigtails and splice tray, 2 cable clamps

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

OBSOLETE

This product was discontinued on: **March 1, 2018**

Product Classification

Product Series	IWB
Product Type	Fiber wall box
Regional Availability	Asia EMEA

Construction Materials

Fiber Mode	Singlemode
Finish	Powder coated
Material Type	Steel
Total Fibers, quantity	48

Dimensions

Depth	140.00 mm 5.51 in
Height	350.00 mm 13.78 in
Width	505.00 mm 19.88 in

Environmental Specifications

Environmental Space	Indoor
Qualification Standards	NEMA type 12

General Specifications

Adapters, quantity	48
Application	Patching Splicing
Cable Stub Type	Pigtails, stranded
Color	Gray
Door, quantity	2
Interface Feature, front	Standard

Interface, front	FC
Package Quantity	1
Packaging Type	Bag Carton
Splice Trays Included, quantity	0
Splicing Capacity, maximum	48
Splicing Type	Mass fusion
Total Ports, quantity	48

Mechanical Specifications

Cable Clamps, quantity	2
Cable Entry Location	Bottom right Top right
Front Door Type	Single hinged
Mount Type	Wall

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

