



IWB Fiber Wall Box, 2-door, singlemode SC/UPC, 48-ports, no pigtails, splice tray, 2 cable clamps

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

Product Series	IWB
Product Type	Fiber wall box
Regional Availability	Asia EMEA

Construction Materials

Fiber Mode	Singlemode
Finish	Powder coated
Material Type	Steel

Dimensions

Depth	140.00 mm 5.51 in
Height	350.00 mm 13.78 in
Width	505.00 mm 19.88 in

Environmental Specifications

Environmental Space	Indoor
Qualification Standards	NEMA type 12

General Specifications

Adapters, quantity	48
Application	Patching Splicing
Color	Gray
Door, quantity	2
Interface Feature, front	Standard
Interface, front	SC
Package Quantity	1
Packaging Type	Bag Carton
Splice Trays Included, quantity	2
Splicing Capacity, maximum	48
Splicing Type	Mass fusion

Total Ports, quantity 48

Mechanical Specifications

Cable Clamps, quantity 2

Cable Entry Location Bottom right | Top right

Front Door Type Single hinged

Mount Type Wall

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

