



## IFDB Fiber Optic Wall Box with 8 SC/APC adapters, with pigtails

- Allows splicing those fibers from an indoor riser cable to the individual drops
- Allows fibers from certain riser cables to be broken out without interrupting the strength member
- Separate storage of un-connected fibers from spliced drop fibers
- Compatible with mechanical, SMOUV and ANT splice protectors
- In-line and butt configuration possible for main riser cable

## Product Classification

<b>Product Type</b>	Fiber wall box
<b>Product Series</b>	IFDB
<b>Regional Availability</b>	EMEA

## General Specifications

<b>Adapters, quantity</b>	8
<b>Color</b>	Light gray
<b>Functionality</b>	Patching   Splitting
<b>Includes</b>	Fiber pigtail assemblies
<b>Interface Feature, input</b>	APC
<b>Interface, input</b>	SC
<b>Package, quantity</b>	12
<b>Packaging Type</b>	Bag   Carton

## Dimensions

<b>Depth</b>	49.00 mm   1.93 in
<b>Height</b>	216.00 mm   8.50 in
<b>Width</b>	126.00 mm   4.96 in

## Mechanical Specifications

<b>Front Cover Type</b>	Screw-on
<b>Material Type</b>	Thermoplastic
<b>Mount Type</b>	Wall   Floor

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

**Flammability Rating** UL 94 V-0  
**Qualification Standard** IEC 60529, IP30

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

