

HomeConnect® 75 Ohm XPRESSPREP® Coaxial Drop Cable, Series 11, black PE jacket with Green Tracer



Product Classification

Brand	HomeConnect® XPRESSPREP®
Product Type	Coaxial drop cable
Product Series	11 Series

Construction Materials

Jacket Material	PE
Center Conductor Material	Copper-clad steel
Dielectric Material	Foam PE
Inner Shield (Braid) Coverage	77 %
Inner Shield (Braid) Gauge	34 AWG
Inner Shield (Braid) Material	Aluminum
Inner Shield (Tape) Material	Aluminum/Polymer/Aluminum (APA) bonded
Outer Shield (Tape) Material	Aluminum/Polymer/Aluminum (APA) bonded

Dimensions

Diameter Over Center Conductor, nominal	1.626 mm 0.064 in
Diameter Over Dielectric, nominal	7.112 mm 0.280 in
Diameter Over Inner Shield (Tape), nominal	7.290 mm 0.287 in
Diameter Over Jacket, nominal	10.160 mm 0.400 in
Jacket Thickness, nominal	0.9906 mm 0.0390 in
Shipping Weight	52.00 lb/kft

Electrical Specifications

dc Resistance, Inner Conductor, nominal	12.50 ohms/kft
dc Resistance, Outer Conductor, nominal	4.30 ohms/kft
dc Resistance, Loop, nominal	16.80 ohms/kft
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
Capacitance	53.1 pF/m 16.2 pF/ft
Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±3 ohm
Nominal Velocity of Propagation (NVP)	85 %

Environmental Specifications

Environmental Space Buried

General Specifications

Cable Type Series 11
Packaging Type Reel
Shield Construction Type Trishield
Center Conductor Gauge 14 AWG
Center Conductor Type Solid
Jacket Color Black
Jacket Marking Feet
Warranty One year

Electrical Performance

Frequency	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5 MHz	1.25	0.38
55 MHz	3.15	0.96
83 MHz	3.87	1.18
85 MHz	3.90	1.19
187 MHz	5.74	1.75
204 MHz	6.14	1.87
211 MHz	6.23	1.90
250 MHz	6.72	2.05
300 MHz	7.38	2.25
350 MHz	7.94	2.42
400 MHz	8.53	2.60
450 MHz	9.02	2.75
500 MHz	9.51	2.90
550 MHz	9.97	3.04
600 MHz	10.43	3.18
750 MHz	11.97	3.65
865 MHz	13.05	3.98
1000 MHz	14.27	4.35
1218 MHz	16.14	4.92
1300 MHz	16.44	5.01
1400 MHz	17.13	5.22
1500 MHz	17.79	5.42
1600 MHz	18.44	5.62
1700 MHz	19.08	5.81
1794 MHz	19.66	5.99
1800 MHz	19.70	6.00
2000 MHz	20.89	6.37
2200 MHz	22.05	6.72
2500 MHz	23.70	7.22
2800 MHz	25.28	7.71
3000 MHz	26.30	8.02

* Attenuation listed represents maximum values at standard condition of 20 °C (68 °F)

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

