



HomeConnect® Locking Terminator, brass

Product Classification

Brand	HomeConnect®
Product Type	Terminator

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Safety Standard	CE EN 60728-4 SCTE

Electrical Specifications

Impedance	75 ohm
Operating Frequency Band	5 – 2000 MHz
Return Loss at Frequency Band, minimum	20 dB @ 1700–2000 MHz 24 dB @ 1002–1700 MHz 25 dB @ 1002–1500 MHz 30 dB @ 5–1002 MHz

General Specifications

Device Type	Locking terminator
Parking Port	Included

Dimensions

Contact Pin Diameter	0.813 mm 0.032 in
Contact Pin Diameter Tolerance	±0.002 in

Mechanical Specifications

Material Type	Brass
Plating	Nickel

Packed Dimensions

Carton Quantity	1250
Height	190.50 mm 7.50 in
Length	330.20 mm 13.00 in
Width	241.30 mm 9.50 in

SVLTA

Shipping Weight

19.05 kg | 42.00 lb

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

