



Undercarpet Flat Copper Cable, 3 conductors, 12 AWG, shielded, 50 ft, white/green/black

- Undercarpet cable with isolated ground is for use with sensitive computer equipment
- Available in 3 and 5-conductor versions

OBSOLETE

This product was discontinued on: December 31, 2022

Product Classification

Regional Availability	North America
Product Type	Power cable
Product Series	Undercarpet

General Specifications

Cable Type	FCC
Conductors, quantity	3
Ground Wire Type	Standard
Jacket Color	Blue
Jacket Color, singles	Black Green White

Dimensions

Height Over Jacket	1.295 mm 0.051 in
Width Over Jacket	70.561 mm 2.778 in
Cable Length	15.24 m 50 ft
Conductor Gauge, singles	12 AWG

Electrical Specifications

Current Rating, maximum, specific	20.0 A @ 20 °C
Safety Voltage Rating	300 V

3-553079-3

Material Specifications

Conductor Material	Bare copper
Insulation Material	PVC

Environmental Specifications

Environmental Space	Indoor
Safety Standard	CSA UL

Packaging and Weights

Packaging Type	Reel
-----------------------	------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

