
LSX-3L1042-A-SPL



LSX Fiber Termination/Splice Panel 2 Ru, 48 - SC/APC, Singlemode Stranded

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series LSX

General Specifications

Functionality Patching | Splicing

Application Used in LSX-style frames only

Cable Stub TypePigtails, stranded

ColorPutty whiteGrowth ConfigurationFully loaded

Interface, front SC/APC

Rack Type EIA 19 in | EIA 23 in

Rack Units 2

Shelf Movement Fixed

Splicing Type Heat shrink, single fiber fusion

Total Ports, quantity 48

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 305 mm | 12.008 in

Material Specifications

Finish Powder coated

Material Type Steel

COMMSCOPE®

LSX-3L1042-A-SPL

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

