

RDT-SJ24J2PD8002A



RapidFiber® FDT Distribution Terminal, 24-position, SC/APC, MPO at far end, 800 ft

Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Brand	RapidFiber®
Product Series	FDT

General Specifications

Adapters, quantity	24
Cable Type	Pigtails - Stranded
Color	Putty white
Interface	SC/APC
Interface, stub	MPO
Mounting	Wall
Port, quantity	24

Dimensions

Height	152.4 mm 6 in
Width	228.6 mm 9 in
Depth	101.6 mm 4 in
Cable Length	243.84 m 800 ft

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

RDT-SJ24J2PD8002A

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA, Type 12

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

