FD3-AC096J00GKBP1



FDH 3000 Fiber Distribution Extra Small Cabinet, 96F, SC/APC, no splitters, single armor loose tube, 100 ft, 12F

Product Classification

Material Type

Regional Availability	North America	
Product Type	Fiber distribution hub	
Product Series	FDH 3000	
General Specifications		
Access	Front	
Cable Type	Armored - Single Loose Tube	
Color	Putty white	
Distribution Cables, quantity	1	
Distribution Ports, quantity	144	
Fibers per Distribution Cable, quantity	96	
Fibers per Feeder Cable, quantity	12	
Interface, Input	SC	
Interface Feature, Input	APC	
Mounting	Pad	
Splitter Slots, quantity	9	
Dimensions		
Height	914 mm 35.984 in	
Width	533 mm 20.984 in	
Depth	356 mm 14.016 in	
Cable Length	30.48 m 100 ft	
Enclosure Size	Extra small	
Material Specifications		
Finish	Powder coated	
Mada and all Terms	Ot I	

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 17, 2023

Steel



FD3-AC096J00GKBP1

Environmental Specifications

Environmental Space

Above ground

Packaging and Weights

Packaging quantity

Packaging Type

Agency

Pallet

1

Regulatory Compliance/Certifications

Classification

CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 17, 2023

