# FDT-BN224NXB0000



iFDT Indoor Fiber Distribution Terminal, 24-fiber, SC/UPC, soft-wall pigtails, heat shrink splice trays

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution terminal

Product Series IFDT

#### General Specifications

Adapters, quantity 24

Cable Entry Location Bottom right | Top right

**Cable Type** Pigtails - Stranded

**Color** Putty white

Front Door Type Double hinged

**Growth Configuration** Fully loaded

Interface SC/UPC

**Lock Type** Padlock ready

**Mounting** Wall

Port, quantity 24

Splice Tray Chip Type Heat shrink

Splicing Capacity, maximum 24

#### Dimensions

 Height
 203.2 mm | 8 in


 Width
 355.6 mm | 14 in

 Depth
 127 mm | 5 in

## Ordering Tree



# FDT-BN224NXB0000



#### Material Specifications

**Finish** Powder coated

Material Type Steel

Optical Specifications

**Fiber Mode** Singlemode

### **Environmental Specifications**

Environmental Space Indoor

**Qualification Standards** NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity



# FDT-BN224NXB0000

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

