

# FL1-6P5BC003

---

FL1000 Fiber Optic Adapter Pack, multimode, ST/UPC, 6 adapters, with pigtails

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	Fiber adapter pack with pigtails
<b>Product Series</b>	FL1000

## General Specifications

<b>Adapters, quantity</b>	6
<b>Cable Type</b>	Pigtails - Stranded
<b>Color</b>	Putty white
<b>Interface</b>	ST
<b>Interface Feature</b>	Standard
<b>Total Fibers, quantity</b>	6

## Dimensions

<b>Height</b>	27.94 mm   1.1 in
<b>Width</b>	149.86 mm   5.9 in
<b>Pigtail Length</b>	3 m   9.843 ft

## Optical Specifications

<b>Fiber Mode</b>	Multimode
-------------------	-----------

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Bag

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value

# FL1-6P5BC003

---

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant

