

# 760217471 | HD-iP-2U-64-MPO-DP-SD



HD iPATCH 2U 64-MPO Distribution Panel, Sliding Panel

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber patch panel   |
| <b>Product Brand</b>         | iPatch®   imVision®   |
| <b>Product Series</b>        | HD  |

## General Specifications

|                              |                 |
|------------------------------|-----------------|
| <b>Color</b>                 | Black           |
| <b>Intelligence Type</b>     | iPatch® enabled |
| <b>Interface, front</b>      | LC/UPC          |
| <b>Rack Units</b>            | 2               |
| <b>Shelf Movement</b>        | Sliding         |
| <b>Total Ports, quantity</b> | 64              |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 88.9 mm   3.5 in     |
| <b>Width</b>  | 482.6 mm   19 in     |
| <b>Depth</b>  | 539.75 mm   21.25 in |

## Material Specifications

|                      |       |
|----------------------|-------|
| <b>Material Type</b> | Steel |
|----------------------|-------|

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>             |
|---------------|-----------------------------------|
| CHINA-ROHS    | Above maximum concentration value |

# 760217471 | HD-iP-2U-64-MPO-DP-SD

---

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant/Exempted

UK-ROHS

Compliant

