

TFP-1TPQ5-021B



TFP Fiber Termination/Splice Panel, 48 LC/UPC, preterminated with pigtailed, singlemode, 1RU, 19 in, black

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	TFP

General Specifications

Functionality	Patching Splicing
Body Style	Symmetrical
Color	Black
Interface, front	LC/UPC
Patch Cord Entry Location	Front, left side Front, right side
Rack Type	EIA 19 in EIA 23 in
Rack Units	1
Shelf Movement	Sliding
Total Ports, quantity	48

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	399.29 mm 15.72 in

Ordering Tree

TFP-1TPQ5-021B

TFP - X X AP X X X X X

Number of Fiber Ports

12	12 fiber ports: 6 LC adapters; 6 SC duplex adapters; 12 ST adapters
24	24 fiber ports: 12 LC adapters

Pack Orientation

L	angle left
R	angle right

Adapter Style

Multimode Connectors	
C3	SC duplex (beige)
C4	SC duplex (aqua)
Q1	LC (beige)
Q2	LC (aqua)
T1	ST®
Singlemode Connectors	
C8	SC UPC duplex (blue)
A2	SC APC duplex (green)
Q5	LC UPC (blue)
T2	ST UPC

Pigtail Length

Leave	Adapters only
Blank	Adapters only
3	3 meter pigtails

Pigtail Type

Leave	Adapters only
Blank	Adapters only
B	Singlemode stranded
E	Multimode stranded

Fiber Size

Leave	Adapters only
Blank	Adapters only
B	OM1 - 62.5/125 Multimode
D	OM3 - 50/125 LOMMF 300m
S	Singlemode

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1
Weight, net	4.649 kg 10.25 lb

Regulatory Compliance/Certifications

TFP-1TPQ5-021B

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant/Exempted

