TFP-4TT00-000B

TFP Fiber Termination/Splice Panel, unloaded, termination only rack/cabinet mount panel, 4 RU, 19 in, black, T-handle latch close

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series TFP

General Specifications

Functionality Patching | Splicing

Body Style Symmetrical

ColorBlackColor, frontBlack

Growth Configuration Unloaded Interface, front Unloaded

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 4

Shelf Movement Fixed

Dimensions

 Height
 177.8 mm | 7 in


 Width
 482.6 mm | 19 in

Depth 399.29 mm | 15.72 in

Ordering Tree



TFP-4TT00-000B



Material Specifications

Finish Powder coated

Material Type Steel

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

-40 °C to +85 °C (-40 °F to +185 °F) **Storage Temperature**

Packaging and Weights

Included Mounting hardware

Packaging quantity

Regulatory Compliance/Certifications

Agency Cla	ssification
------------	-------------

CHINA-ROHS Below maximum concentration value

Classification

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

COMMSCOPE®

TFP-4TT00-000B

UK-ROHS

Compliant

