



## SYSTIMAX 360™ Evolve 48-port flat panel

### Product Classification

**Regional Availability**

Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio**

SYSTIMAX®

**Product Type**

RJ45 patch panel

**Product Brand**

SYSTIMAX 360™

**Product Series**

M Series

### General Specifications

**Cable Type**

Unshielded

**Color**

Cool gray

**Modules, quantity**

48

**Panel Style**

Straight

**Rack Type**

EIA 19 in

**Rack Units**

2

**Total Ports, quantity**

48

**Wiring**

T568A | T568B

### Dimensions

**Height**

88.9 mm | 3.5 in

**Label Height**

10.922 mm | 0.43 in

**Width**

482.6 mm | 19 in

**Depth**

43.18 mm | 1.7 in

**Depth, with cable management**

172.72 mm | 6.8 in

**Label Length**

33.782 mm | 1.33 in

**Compatible Diameter Over Dielectric, maximum**

1.168 mm | 0.046 in

**Compatible Diameter Over Dielectric, minimum**

0.762 mm | 0.03 in

# 760187195 | 360-E-MOD-2U-48

---

## Electrical Specifications

<b>Current Rating at Temperature</b>	1.5 A @ 20 °C   1.5 A @ 68 °F
<b>Dielectric Withstand Voltage, RMS, conductive surface</b>	1,500 Vac @ 60 Hz
<b>Dielectric Withstand Voltage, RMS, contact-to-contact</b>	1,000 Vac @ 60 Hz
<b>Insulation Resistance, minimum</b>	500 MOhm

## Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Powder-coated steel
----------------------	---

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	1.043 kg   2.3 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

