



## 1100 ANGLED GS3 PANEL KIT - 2U

### Product Classification

**Regional Availability**

Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio**

SYSTIMAX®

**Product Type**

RJ45 patch panel

### General Specifications

**ANSI/TIA Category**

6

**Cable Type**

Unshielded

**Color**

Black

**Modules, quantity**

8

**Panel Style**

Angled

**Rack Type**

EIA 19 in

**Rack Units**

2

**Total Ports, quantity**

48

### Dimensions

**Height**

88.9 mm | 3.5 in

**Width**

482.6 mm | 19 in

**Depth**

210.82 mm | 8.3 in

### Electrical Specifications

**Current Rating at Temperature**

1.5 A @ 20 °C | 1.5 A @ 68 °F

**Dielectric Withstand Voltage, RMS, conductive surface**

1,500 Vac @ 60 Hz

**Dielectric Withstand Voltage, RMS, contact-to-contact**

1,000 Vac @ 60 Hz

### Material Specifications

**Material Type**

Powder-coated steel

### Mechanical Specifications

# 760206920 | 1100A-U-GS3-KIT-2U

---

**Plug Insertion Life, test plug**

IEC 60603-7 compliant plug

## Environmental Specifications

**Operating Temperature**

-10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature**

-40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity**

Up to 95%, non-condensing

**Flammability Rating**

UL 94 V-0

**Safety Standard**

UL | cUL

## Packaging and Weights

**Packaging quantity**

1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

