760220418 | 360CM12-4x6-TS





Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®
Product Type Fiber module

General Specifications

Functionality Breakout

Adapters, quantity, front 6
Adapters, quantity, rear 4

Color, frontBlueColor, housingBlackColor, rearBlue

Data Module TypeStandardInterface, frontMPOInterface Feature, frontStandard

Interface, rear MPO

Interface Feature, rear Male | Reduced footprint

Polarity Method B

Shuttered No
Total Fibers, quantity 24
Total Ports, quantity, front 6

Dimensions

 Height
 27.94 mm | 1.1 in

 Width
 91.44 mm | 3.6 in

COMMSCOPE®

760220418 | 360CM12-4x6-TS

Depth 109.22 mm | 4.3 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED® | OS2

Insertion Loss Change, mating0.3 dBInsertion Loss Change, temperature0.3 dBInsertion Loss, maximum1.34 dB

Environmental Specifications

Safety Standard UL

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant/Exempted



* Footnotes

Insertion Loss Change, matingMaximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

