

760239080 | UDS-6U-BK-LC-B-ULL



UDS 6RU splice panel, 432 duplex LC/UPC ports, Enhanced Method B, ULL

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	UDS

General Specifications

Application	Preloaded with 36 UDS modules
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	LC/UPC
Pigtail Assembly Type	12-fiber, ribbon
Pigtails Included, quantity	36
Rack Type	EIA 19 in
Rack Units	6
Shelf Movement	Sliding, rear
Splice Trays Included, quantity	12

Dimensions

Height	266.7 mm 10.5 in
Width	444.5 mm 17.5 in
Depth	609.6 mm 24 in

Optical Specifications

Insertion Loss, maximum	0.25 dB
--------------------------------	---------

Environmental Specifications

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Weight, net 20.412 kg | 45 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant

