

FD3-PA060J2CU3520



FDH 3000 Fiber Distribution Hub in a Pedestal, 60F, SC/APC, (2) 16-splr. module, stranded pigtails, 72 splice cap., 21F feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

Product Classification

| | |
|------------------------------|-------------------|
| Regional Availability | North America |
| Product Type | Hub in a pedestal |
| Product Series | FDH 3000 |

General Specifications

| | |
|-------------------------------------|-------------|
| Access | Front |
| Color | Putty white |
| Distribution Ports, quantity | 60 |
| Mounting | Pad |

Dimensions

| | |
|-----------------------|-------|
| Enclosure Size | Small |
|-----------------------|-------|

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Environmental Specifications

| | |
|----------------------------|--------------|
| Environmental Space | Above ground |
|----------------------------|--------------|

Packaging and Weights

| | |
|---------------------------|--------|
| Packaging quantity | 1 |
| Packaging Type | Pallet |

FD3-PA060J2CU3520

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

