760238448 | OCM6-SP318L2-16DB1



OCM6 Fiber Optic Splitter Module, Planar, three 1x8 Splitters, singlemode, LC/APC, symmetrical split ratio, butt style, 1.6 m pigtails

Product Classification

Regional Availability EMEA

PortfolioCommScope®Product TypeSplitter module

Product Series OCM6

General Specifications

Device Type Standard VAM

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Application For use with BUDI wall boxes

Circuits, quantity 3

Distribution Type 1 x 8 splitter

 Interface, Input
 LC

 Interface Feature, Input
 APC

 Interface, Output
 LC

 Interface Feature, Output
 APC

Split Ratio Symmetrical

Splitter, quantity 3

Dimensions

 Height
 130 mm | 5.118 in

 Width
 49.8 mm | 1.961 in

 Depth
 16.5 mm | 0.65 in

 Pigtail Length, Input
 1.6 m | 5.249 ft

Page 1 of 2



760238448 | OCM6-SP318L2-16DB1

Pigtail Length, Output 1.6 m | 5.249 ft

Pigtail Diameter 1.8 mm | 0.071 in

Packaging and Weights

Packaging quantity 1

