

OCMF LGX Fiber Optic Module, CWDM, Mux, LC/APC, 11 channels, starting wavelength 1310 nm

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	CWDM module
<b>Product Series</b>	LGX

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Multiplexing
<b>Application</b>	For use with LGX panels
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	11-channel CWDM
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC
<b>Multiplexers, quantity</b>	1

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted

