

760242560 | CPP-6A-UDDM-SL-1U-24



Unshielded Discrete Distribution Module Panel, Cat 6A, SL, 1U, 24 port, Black

Product Classification

Regional Availability Australia/New Zealand | Europe

Portfolio CommScope®

Product Type RJ45 patch panel

General Specifications

ANSI/TIA Category 6A

Cable Type Unshielded

Color Black

Growth Configuration Fully loaded

Panel Style Straight

Rack Type EIA 19 in

Rack Units 1

Total Ports, quantity 24

Transmission Standards ANSI/TIA-568.2-D | ISO/IEC 11801 Class EA

Dimensions

Height 44.45 mm | 1.75 in

Width 482.6 mm | 19 in

Depth, with cable management 119.38 mm | 4.7 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Powder-coated steel

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

760242560 | CPP-6A-UDDM-SL-1U-24

Flammability Rating UL 94 V-0
Safety Standard RCM | UL | cUL

Packaging and Weights

Included Modular jacks (24)
Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

