

CK6347-000 | FIST-GPS2-J-48KIT-CO

FIST-GPS2 Fiber Termination/Splice Panel, 48 ports, 2RU, 19 in, gray

Product Classification

| | |
|------------------------------|--------------------------|
| Regional Availability | EMEA |
| Portfolio | CommScope® |
| Product Type | Fiber patch/splice panel |
| Product Brand | FIST® |
| Product Series | FIST-GPS2 |

General Specifications

| | |
|-----------------------|------------------------------------|
| Functionality | Patching Splicing |
| Application | Used in FIST-GR3-style frames only |
| Color | Gray |
| Color, front | Gray |
| Rack Type | EIA 19 in ETSI 600 mm |
| Rack Units | 2 |
| Shelf Movement | Sliding |

Dimensions

| | |
|---------------|------------------|
| Height | 88.9 mm 3.5 in |
| Width | 482.6 mm 19 in |

Material Specifications

| | |
|----------------------|------------------|
| Finish | Powder coated |
| Material Type | Galvanized steel |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -5 °C to +45 °C (+23 °F to +113 °F) |
| Storage Temperature | -30 °C to +60 °C (-22 °F to +140 °F) |
| Relative Humidity | Up to 93%, non-condensing |

Packaging and Weights

| | |
|-----------------|-------------------|
| Included | Mounting hardware |
|-----------------|-------------------|

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

