CX4165-000 | FIST-GPS3-Q-1



FIST-GPS3 Fiber Panel for holding up to 6 GPST Patch/Splice Trays, unloaded, 3RU, 15 in, gray

Product Classification

Regional Availability EMEA

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Brand FIST®

Product Series FIST-GPS3

General Specifications

Functionality Patching | Splicing

Application Used in FIST-GR3F-style frames only

Color Gray
Color, front Gray

Growth Configuration Unloaded
Interface, front Unloaded
Rack Type EIA 15 in

Rack Units 3

Shelf Movement Sliding

Dimensions

 Height
 125 mm | 4.921 in

 Width
 381 mm | 15 in

 Depth
 280 mm | 11.024 in

Material Specifications

Finish Powder coated

COMMSCOPE®

CX4165-000 | FIST-GPS3-Q-1

Material Type Galvanized steel

Environmental Specifications

Operating Temperature -5 °C to +45 °C (+23 °F to +113 °F)

Storage Temperature -30 °C to +60 °C (-22 °F to +140 °F)

Relative Humidity Up to 93%, non-condensing

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

