



CHD ULL Multimode OM4 Splice Cassette, 12LC, with dust plugs and pigtails

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Brand	SYSTIMAX ULL
Product Series	CHD

General Specifications

Color, front	Aqua
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Polarity	Method B Enhanced
Shuttered	No
Total Fibers, quantity	12

Dimensions

Height	12.446 mm 0.49 in
Width	83.82 mm 3.3 in
Depth	184.658 mm 7.27 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4, LazrSPEED® 550
Insertion Loss, maximum	0.15 dB

Environmental Specifications

760244973 | CHD-SP-12LC-LS-B-ULL

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Included Single Fusion Splice Protection Sleeves

Packaging quantity 1

Weight, net 0.095 kg | 0.21 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant



Included Products

- FST-ACC005 – Fiber Optic Protective Splice Sleeve, 1 package

FST-ACC005



Fiber Optic Protective Splice Sleeve, 1 package

Product Classification

Regional Availability North America
Product Type Fiber protection sleeve

General Specifications

Splicing Type Heat shrink, single fiber fusion

Environmental Specifications

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

