

# 760245734 | CHD-SP-12LC-LSR-AS-ULL

---

CHD ULL Multimode OM4 Splice Cassette, 12LC, with dust plugs and ribbon pigtails

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber cassette with ribbon pigtail                                  |
| <b>Product Brand</b>         | SYSTIMAX ULL  |
| <b>Product Series</b>        | CHD   |

## General Specifications

|                               |                            |
|-------------------------------|----------------------------|
| <b>Color, front</b>           | Aqua                       |
| <b>Interface, front</b>       | LC/UPC                     |
| <b>Interface, rear</b>        | Ribbon pigtail             |
| <b>Polarity</b>               | Method A   Pairs, straight |
| <b>Shuttered</b>              | No                         |
| <b>Total Fibers, quantity</b> | 12                         |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 12.446 mm   0.49 in  |
| <b>Width</b>  | 83.82 mm   3.3 in    |
| <b>Depth</b>  | 184.658 mm   7.27 in |

## Optical Specifications

|                                |                     |
|--------------------------------|---------------------|
| <b>Fiber Mode</b>              | Multimode           |
| <b>Fiber Type</b>              | OM4, LazrSPEED® 550 |
| <b>Insertion Loss, maximum</b> | 0.15 dB             |

## Environmental Specifications

|                                |                           |
|--------------------------------|---------------------------|
| <b>Qualification Standards</b> | IEC 61753-1   TIA-568.3-D |
| <b>Safety Standard</b>         | CE   CSA   UL             |

## Packaging and Weights

|                 |                                       |
|-----------------|---------------------------------------|
| <b>Included</b> | Mass Fusion Splice Protection Sleeves |
|-----------------|---------------------------------------|

**Packaging quantity** 1  
**Weight, net** 0.095 kg | 0.21 lb

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## Included Products

- FST-ACC006 – Fiber Optic Protective Splice Sleeve, 12f mass fusion, 1 each