

E47265-000 | PED-CAP-R-4L-INT



PEDCAP Copper Closure, butt, unpressurized, heat shrink, 350 mm joint length, for up to 6 cables

- One piece end cap with heat-shrinkable outlet for sealing onto the cables
- Provides an excellent environmental and mechanical seal for telephone splices in the distribution network
- Suitable for use as an overhead, underground or pedestal joint closure in both new construction and maintenance applications

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Unpressurized heat shrink closure
Product Series	PEDCAP

General Specifications

Application	For use with Polyethylene and metal jacketed cables
Cable Capacity, maximum	6
Cable Sealing Type	Hotmelt adhesive
Closure Style	Single-ended
Color	Black
Mounting	Pedestal
Splicing Capacity, maximum	200

Dimensions

Length	520 mm 20.472 in
Single Cable Diameter, maximum	60 mm 2.362 in
Single Cable Diameter, minimum	25 mm 0.984 in
Splice Bundle Diameter, maximum	84 mm 3.307 in
Sheath Opening, nominal	350 mm 13.78 in

Material Specifications

E47265-000 | PED-CAP-R-4L-INT

Material Type Polyolefin

Environmental Specifications

Environmental Space Aerial | Buried

Packaging and Weights

Included Aluminum closing strip | Aluminum foil | Cleaning tissues | Desiccant | Tie wraps

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

