F07891-000 | VCKT-160-12-INT



VCKT Vault Copper Closure, unpressurized, heat shrink, 740 mm joint Flength, 12 MDF cable outlets

- Vault closure system for the distribution of telecommunication cables in telephone exchanges
- Flexibility arises from selective use of break-out ports up to 3/9/12 or 24 MDF cables
- Vertical installation with re-entry option of the splice area for testing and measuring

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability EMEA

Product Type Unpressurized heat shrink closure

Product Series VCKT

General Specifications

Application For use with Polyethylene and metal jacketed cables

Branch-off ClipTo be ordered seperately

Cable Capacity, maximum 13

Cable Sealing Type Hotmelt adhesive

Closure Style Single-ended

Color Black

Splice Protection Type Metal canister

Dimensions

Length950 mm | 37.402 inSingle Cable Diameter, maximum36 mm | 1.417 inSingle Cable Diameter, minimum12 mm | 0.472 inSplice Bundle Diameter, maximum158 mm | 6.22 inSheath Opening, nominal740 mm | 29.134 in



F07891-000 | VCKT-160-12-INT

Environmental Specifications

Environmental Space Above ground | Below ground | Buried

Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible

stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity

wire | Underclips

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

