

# FL2-24TS525-B



FL2000 Fiber Termination/Splice Panel, unloaded, 24 Ports, 3RU, 19 in, black

## Product Classification

|                       |                               |
|-----------------------|-------------------------------|
| Regional Availability | Latin America   North America |
| Portfolio             | CommScope®                    |
| Product Type          | Fiber patch/splice panel      |
| Product Series        | FL2000                        |

## General Specifications

|                            |                                    |
|----------------------------|------------------------------------|
| Functionality              | Patching   Splicing                |
| Cable Exit Location        | Rear, left side   Rear, right side |
| Color                      | Black                              |
| Color, front               | Black                              |
| Growth Configuration       | Unloaded                           |
| Interface, front           | Unloaded                           |
| Patching Capacity, maximum | 24                                 |
| Rack Type                  | EIA 19 in                          |
| Rack Units                 | 3                                  |
| Shelf Movement             | Hinged                             |
| Splicing Capacity, maximum | 24                                 |
| Total Ports, quantity      | 24                                 |

## Dimensions

|        |                     |
|--------|---------------------|
| Height | 133.35 mm   5.25 in |
| Width  | 482.6 mm   19 in    |
| Depth  | 256.54 mm   10.1 in |

## Material Specifications

|               |               |
|---------------|---------------|
| Finish        | Powder coated |
| Material Type | Steel         |

# FL2-24TS525-B

---

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Storage Temperature</b>   | -40 °C to +85 °C (-40 °F to +185 °F) |

## Packaging and Weights

|                           |                   |
|---------------------------|-------------------|
| <b>Included</b>           | Mounting hardware |
| <b>Packaging quantity</b> | 1                 |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

