

FVM-VLM19X700-FCM

FVM, LGX compatible Fiber Panel, unloaded, 4RU, 19 in, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FVM LGX

General Specifications

Functionality	Multiplexing Splitting
Application	Used in rear-load FDF-style frames only
Body Style	Symmetrical
Color	Putty white
Color, front	Putty white
Growth Configuration	Unloaded
Interface, front	Unloaded
Patch Cord Entry Location	Front, left side Front, right side
Rack Type	EIA 19 in
Rack Units	4
Shelf Movement	Fixed

Dimensions

Height	177.8 mm 7 in
Depth	304.8 mm 12 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

Packaging and Weights

FVM-VLM19X700-FCM

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

