

# DLX® Fiber Indexing Terminal, no Splitter, 1 Forward Port, 1 Reverse Port, Dielectric Loose Tube Cable, 350 Feet

- Fiber Indexing terminals are access terminals using hardened connectivity technology that withstand the rugged outside plant environment
- Fiber Indexing terminals eliminate splicing and use 12-strand fiber cable in a daisy-chain topology, reducing the total required cable length by up to 70%
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and play drop cable installations

#### Product Classification

North America
Access terminal, indexed without splitter/tap
DLX®
NDX
Dielectric - Flat - Loose Tube
1
1 port
Black
Hardened mini-size (DLX) adapter
1
Handhole   Pedestal   Pole
Hardened multi-fiber (HMFOC) jack, male/pinned
1
Hardened mini-size DLX
1
0
Hardened multi-fiber (HMFOC) plug
297.8 mm   11.724 in
130.3 mm   5.13 in

Page 1 of 4




Depth

Cable Length, stub

**Cable Outer Diameter** 

90.4 mm | 3.559 in 350 ft (106 m) 4.5 x 8.1 mm (0.18 x 0.32 in)






### Ordering Tree

Page 2 of 4





#### Material Specifications

Enclosure Material Type	Gasketed hardened plastic
Optical Specifications	
Fiber Type	G.652.D
Operating Wavelength Range	1260 – 1635 nm
Attenuation Cable Coefficient, maximum	0.30 dB/km @ 1550 nm   0.40 dB/km @ 1310 nm
Attenuation Terminal Connectors, maximum	0.45 dB
Directivity, minimum	60 dB
Insertion Loss, Stub Connector, maximum	0.45 dB
Insertion Loss, Stub Connector, typical	0.16 dB
Insertion Loss, Terminal Connector, typical	0.16 dB
Return Loss, Connector, minimum	65 dB

#### **Environmental Specifications**

#### **Operating Temperature**

-40 °C to +70 °C (-40 °F to +158 °F)

Page 3 of 4



Relative Humidity	5%–100%, condensing
Environmental Space	Above ground   Below ground   Buried
Flammability Rating	UL 94 V-0
Qualification Standards	IEC 60529, IP68 + 2 m waterhead   NEMA, Type 6 + 10 ft waterhead   Telcordia GR-3120-CORE   Telcordia GR-326- CORE   Telcordia GR-771-CORE
UV Resistance	UV stabilized
Packaging and Weights	
Included	Enclosure (1)   Universal mounting bracket (1)
Packaging quantity	1
Packaging Type	Box   Carton
Weight, without cable	1 kg   2.205 lb

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



#### Included Products

MST-UMB-MINI – DLX® Mini-MST, Fiber Optic Universal Mounting Bracket

Page 4 of 4

