

C600-BNFNM

CNT-600 CNT® Jumper with interface types N Female Bulkhead and N Male



OBSOLETE

This product was discontinued on: August 14, 2022

Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-600

General Specifications

Attachment, Connector A	Field attachment
Attachment, Connector B	Field attachment
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-600
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Length	0 m 0 ft
Nominal Size	0.600 in

VSWR/Return Loss

C600-BNFM

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	14.99

Jumper Assembly Sample Label



Included Products

- 600BPNM-C — Type N Male for CNT-600 braided cable
- CNT-600-FR — CNT-600-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket, Dca s2 d2 Compliant