## CGAAB | IPO6-06PUTP-01S-01S

#### **Base Product**



InstaPATCH® Cu GigaSPEED XL® U/UTP Plenum Preterminated Copper Cable, single row standard density outlet to single row standard density outlet, 6 links

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Copper trunk cable assembly

Product Brand GigaSPEED XL® | InstaPATCH® Cu

General Specifications

ANSI/TIA Category 6

Cable Type U/UTP (unshielded)

Conductor Type Solid

Interface, Connector A Information outlet

Interface Feature, connector A Single row | Standard density

Interface, Connector B Information outlet

Interface Feature, connector B Single row | Standard density

Link Count 6

Wiring T568B

**Dimensions** 

Cable Assembly Length Range (m)2-90Cable Assembly Length Range (ft)7-295


**Electrical Specifications** 

dc Resistance, maximum0.3 ohmSafety Voltage Rating300 V

Ordering Tree



# CGAAB | IPO6-06PUTP-01S-01S



## **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$ 

Environmental Space Plenum
Flammability Rating UL 94 V-0

## Regulatory Compliance/Certifications

Agency C	Classification
CHINA-ROHS E	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC C	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS C	Compliant



#### Included Products

2071E-4/23 – GigaSPEED XL® 2071E ETL Verified Category 6 U/UTP Cable, plenum, 4 pair

count

MGS400 – GigaSPEED XL® M-Series Modular Jack, RJ45, Cat6 Unshielded

