FNWLASAAF

Base Product



SingleMode LC/APC to SC/APC, Ruggedized Fiber Fanout Cable Assembly, 24-Fiber, Low Smoke Zero Halogen (LSZH)

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX InstaPATCH® 360

Ordering NoteFor lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration | Not available in the United States or Canada

General Specifications

Color, boot AGreenColor, connector AGreenColor, boot BGreenColor, connector BGreen

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A LC/APC
Interface, Connector B SC/APC

Jacket Color Yellow

Fibers per Subunit, quantity 12

Total Fibers, quantity 24

Dimensions


Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 8 - 999

COMMSCOPE®

FNWLASAAF

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



FNWLASAAF



Included Products

460125222 460125784

760050351 N-024-MP-8W-F12YL/D - TeraSPEED® LC APC Connector for 1.6 mm Fiber, Duplex, Singlemode, green

- TeraSPEED® SC APC Connector for 1.6 mm Fiber, Duplex, Singlemode, green

Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 24 fiber with 12 fiber subunits, Gel-free, Singlemode G.652.D and G.657.A1, Feet jacket marking, Yellow jacket color, Dca flame rating