

# 244813-1M5

---

CNT-240 CNT® Jumper with interface types N Male and N Female, 1.5 m



**OBSOLETE**

## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Brand</b>	CNT®
<b>Product Series</b>	CNT-240

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Cable Family</b>	CNT-240
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	N Female
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	1.5 m   4.921 ft
<b>Nominal Size</b>	0.240 in

## Electrical Specifications

<b>DTF, Connector A</b>	-28 dB
<b>DTF, Connector B</b>	-21 dB

## VSWR/Return Loss

**Frequency Band**

# 244813-1M5

0-2100 MHz

## Jumper Assembly Sample Label



## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## Included Products

- 240BPNM-C-CR – Type N Male for CNT-240 braided cable
- 240PTM-CR – TNC Male for CNT-240 braided cable
- CNT-240 – CNT-240, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket