

244813-M5

CNT-195 CNT® Jumper with interface types N Male and TNC Male, 0.5 m



OBSOLETE

Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-195

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-195
Interface, Connector A	N Male
Interface, Connector B	TNC Male
Specification Sheet Revision Level	A

Dimensions

Length	0.5 m 1.64 ft
Nominal Size	0.195 in

Electrical Specifications

DTF, Connector A	-26 dB
DTF, Connector B	-28 dB

VSWR/Return Loss

Frequency Band

244813-M5

0-2700 MHz

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted



Included Products

195PNM-CR	- Type N Male for CNT-195 braided cable
195PTM	- TNC Male for CNT-195 braided cable
419001003/10 CNT-195-P-6G	- CNT-195, CNT [®] 50 Ohm Braided Coaxial Cable, white plenum CMP(ETL) C(ETL), fire retardant.
CNT-195-FR	- CNT-195-FR, CNT [®] 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket, Dca s2 d2 Compliant
CNT-195-P	- CNT-195, CNT [®] 50 Ohm Braided Coaxial Cable, white plenum CMP(ETL) C(ETL), fire retardant.