

# RG142-TNMNM-3M

---

RG142 Braided Jumper with interface types N Male and N Male, 3 m



**OBSOLETE**

## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Series</b>	RG142

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Cable Family</b>	RG142
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	N Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	3 m   9.843 ft
---------------	----------------

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
700–3000 MHz	1.152	23.02

## Jumper Assembly Sample Label

# RG142-TNMNM-3M



## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## Included Products

RG142TNM-CR – Type N Male for RG142 braided cable