



RJ45 Consolidation Point Cable, plug to jack, S/FTP, white, 7.5 m

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair patch cord

## General Specifications

<b>ANSI/TIA Category</b>	6A
<b>Cable Type</b>	S/FTP (shielded)
<b>Interface, Connector A</b>	RJ45 plug
<b>Interface, Connector B</b>	AMP-TWIST jack
<b>Jacket Color</b>	White
<b>Pairs, quantity</b>	4
<b>Transmission Standards</b>	IEEE 802.3bt Type 4

## Dimensions

<b>Cord Length</b>	7.5 m   24.606 ft
<b>Compatible Conductor Gauge, stranded</b>	26 AWG

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

# 1-1711420-4

---

**Agency**

CHINA-ROHS

REACH-SVHC

ROHS

**Classification**

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant